




DB
2 labbri
lamiera esterna




DC2Y
2 labbri




DCR2
2 labbri



DCY
2 labbri




HSCJ
1 labbro




HSCR
1 labbro




HSCRY
1 labbro




HTCL
1 labbro
+ parapolvere




HTCYL
1 labbro
+ parapolvere




KC
senza molla
+ parapolvere




SB
1 labbro
lamiera esterna




SC
1 labbro




SCY
1 labbro




TBY
1 labbro
+ parapolvere
lamiera esterna




TC
1 labbro
+ parapolvere




TCJ
1 labbro
+ parapolvere




TCL4Y
2 labbri
+ parapolvere



TCY
1 labbro
+ parapolvere



TG6
1 labbro
+ 2 parapolvere



VC
senza molla